



MR multirailclamp

Product information

General:

The MR Multi-rail grabs have been designed to facilitate the fastbulk handling of a specific rail section (details to be advised at time of order). Rails are locked onto the clamp by swivelling feet that locate under the rail-head and top clamp body that rotates in a cam action pressing a hard rubber lined horizontal beam onto the top of the rail-head. The rubber lined contact beam prevents marking or damage to the rail-head. Two clamps are recommended at centres of 50% to 60% of rail length for rails up to 20 mtr long. For rails longer than 20mtr, three clamps at centre distance between outer clamps of 65% to 75% of rail length must be used. (NB. Clamp must be within rated WLL). Rails to be lifted must be stacked with bottom flange toes touching. All rails must be of the same rail section size.

Part code	WLL ton	Type	Number of rails	Weight kg
50215000000110	5	MR3	3	84
50215000000114	5	MR4	4	108
50215000000115	5	MR5	5	132
50216000000110	6	MR6	6	156
50217000000110	7	MR7	7	180
50218000000110	8	MR8	8	204
50211000000110	10	MR10	10	252
50211200000110	12	MR12	12	300